

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0534050410](#)
Status: **Obsolete**
Description: 3.96mm (.156") Pitch SPOX™ Header, Vertical, with Friction Lock, 4 Circuits

Documents:

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	53405
Application	Power, Wire-to-Board
Obsolete Date	2004/08/01
Product Name	SPOX™

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Durability (mating cycles max)	30
Flammability	94V-0
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.60mm (.142")
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Bag
Pitch - Mating Interface	3.96mm (.156")
Polarized to PCB	No
Shrouded	Partial
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C


Electrical

Current - Maximum per Contact	7A
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers

Product Specification	PS-5195-003, PS-5195-007, RPS-5195-001
Sales Drawing	SD-53405-001



Series
image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[53405Series](#)

Mates With

[5195](#)