

Dome Plugs



This nylon dome plug is ideal for covering unwanted openings, with its convex, matt finished head tapering to a thin edge for an excellent appearance. As the dome plugs are manufactured from nylon 6,6 they offer a good resistance to most solvents, aromatic hydrocarbons, dilute alkalis, detergents, oils, greases, and fats. They also offer a limited resistance to dilute acids and offer a short term working temperature

between -40 and 100°C. The dome plug is quick and easy to install. Fingertip pressure will lock the dome plug firmly into panels to provide a neat finish. The plug head height is only 1.6mm.

| UL/CSA Description | Mounting Hole Diameter (mm) | Max. Chassis Thickness (mm) | Plug Head Diameter (mm) | Overall Height (mm) |
|--------------------|-----------------------------|-----------------------------|-------------------------|---------------------|
| DP-187             | 4.8                         | 1.6                         | 6.4                     | 5.9                 |
| DP-250             | 6.4                         | 1.6                         | 7.9                     | 7.9                 |
| DP-312             | 8.0                         | 1.6                         | 9.5                     | 7.9                 |
| DP-375             | 9.5                         | 3.2                         | 11.9                    | 10.3                |
| DP-437             | 11.0                        | 3.2                         | 13.5                    | 10.3                |
| DP-500             | 12.7                        | 3.2                         | 14.7                    | 10.3                |
| DP-562             | 14.3                        | 3.2                         | 16.7                    | 10.3                |
| DP-625             | 15.9                        | 3.2                         | 18.2                    | 10.3                |
| MDP-16             | 16.0                        | 2.5                         | 18.5                    | 10.3                |
| DP-687             | 17.5                        | 3.2                         | 19.8                    | 10.3                |
| DP-750             | 19.0                        | 3.2                         | 23.4                    | 10.3                |
| MDP-20             | 20.0                        | 2.5                         | 22.6                    | 10.3                |
| DP-812             | 20.6                        | 3.2                         | 22.6                    | 10.3                |
| DP-875             | 22.2                        | 3.2                         | 25.8                    | 11.5                |
| MDP-25             | 25.0                        | 2.5                         | 29.8                    | 11.5                |
| DP-1000            | 25.4                        | 3.2                         | 30.6                    | 11.5                |
| DP-1093            | 27.8 - 28.6                 | 3.2                         | 30.9                    | 11.5                |

492107

| UL/CSA Description | Pack Qty | Order Code | Price Per Pack |
|--------------------|----------|------------|----------------|
| DP-187             | 25       | 151-4449   |                |
| DP-250             | 25       | 151-4450   |                |
| DP-312             | 25       | 151-4451   |                |
| DP-375             | 25       | 151-4452   |                |
| DP-437             | 25       | 151-4454   |                |
| DP-500             | 25       | 151-4455   |                |
| DP-562             | 25       | 151-4456   |                |
| DP-625             | 25       | 151-4457   |                |
| MDP-16             | 25       | 151-4458   |                |
| DP-687             | 25       | 151-4459   |                |
| DP-750             | 25       | 151-4460   |                |
| MDP-20             | 25       | 151-4461   |                |
| DP-812             | 25       | 151-4462   |                |
| DP-875             | 25       | 151-4463   |                |
| MDP-25             | 25       | 151-4464   |                |
| DP-1000            | 25       | 151-4466   |                |
| DP-1093            | 25       | 151-4467   |                |