



SPECIFICATIONS SHEET

PRODUCT TYPE : EXTERNAL DRIVE PIEZO TRANSDUCER

PRODUCT SERIES : DB-E1548

DESCRIPTION : PZ TRANSDUCER 5V L/W ABS SP RoHS


COLOR : BLACK

ELECTRICAL SPECIFICATIONS

MODEL NO.	154PZ14480LF - LA
SOUND PRESSURE LEVEL	80.0 dBA min. (5.0V p-p Square Wave , 10 cm , 4800 Hz)
CAPACITANCE	12000 pF $\pm$ 30 % at 120 Hz
* MAX. INPUT VOLTAGE	30.0 V p-p
OPERATING TEMPERATURE	-20 ~ +60 °C
TERMINAL	LEADWIRE (UL1571 , AWG#30)
HOUSING MATERIAL	ABS
* WEIGHT	3.0 g

DIMENSIONS

UNIT : mm



Approved By : 
Date : 20-Jun.-2006



Prepared By : 
Date : 20-Jun.-2006



Modify :	Date :	By :