



DCD985M2

18V XR Li-Ion Premium Hammer Drill Driver

Selling Proposition

- 18V XR Li-Ion XRP hammer drill driver featuring XR 4.0Ah Li-Ion battery technology
- Tough 3 speed all metal transmission for increased runtime and longer tool life
- 22 position adjustable torque control for optimised precision when screw driving
- 13mm ratcheting keyless chuck with automatic spindle lock for fast bit changes
- Efficient intelligent trigger allowing total control over all applications
- LED with delay feature for improved visibility and flashlight functionality

Standard Equipment

- 2 x 4.0Ah XR Li-Ion battery packs with state of charge indicator
- Multi-voltage XR charger
- Belt hook
- Magnetic bit holder
- Multi position side handle

Warranty Specifications

- 3 year limited warranty
- 30 Day Money Back Guarantee
- 1 Year Free Service Contract

Specifications

Battery chemistry	XR Li-Ion
Voltage	18 V
Battery Capacity	4.0 Ah
Max Torque (Hard)	80 Nm
Max Torque (Soft)	38 Nm
Power Output	500 Watt
No Load Speed	0-575/1350/2000 rpm
Beats per Minute	0-9755/22950/34000 bpm