

Heavy-Duty Computer Power Extension Cord for Servers and Computers, 20A, 12AWG (IEC-320-C19 to IEC-320-C20), 6-ft.

MODEL NUMBER: **P036-006**



Highlights

- C19 to C20 Power Cable, 6ft
- 12AWG x 3C, 20 Amp Rated
- RoHS Compliant

Package Includes

- C19 to C20 Power Cable, 6ft.

Description

Use Tripp Lite's P036-006 in server applications that require a higher rated, heavier gauge cable. C19 to C20 connectors, 3 x 12ga conductors, 20A rated, 250V - ideal for use with Blade Server Chassis.

Features

- Molded, Heavy-Duty Power Cable, 6ft.
- IEC-60320-C19 to IEC-60320-C20
- 12AWG x 3C, SJTW, 20A, 250Volt
- RoHS Compliant

Specifications

SELECTOR	
Selector Type	CABLES
General Info	
Product Group	POWER CORDS
TAA Compliant	No
OVERVIEW	
Intended Application	Powering Devices
Style	Power Cables

Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.83
UPC ASSIGNMENT	
Unit Carton UPC#	037332141620
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	IEC-320-C20
Connector B	IEC-320-C19
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.