

AVD50 Series

50 Watts

Data Sheet


Total Power: 50 Watts
Input Voltage: 36 - 75V
of Outputs: Single

SPECIAL FEATURES

- 2:1 wide input range
- Optimised for high density, small space applications
- Low ripple and noise
- Fixed switching frequency
- High efficiency
- High capacitive load capability
- Pre-bias start-up capability
- Basic insulation system
- Through-hole or SMT termination
- Openframe structure
- Two year warranty

SAFETY

- UL, cUL: UL60950
- TUV/CE: IEC/EN60950



Electrical Specifications


Input	
Input range	36 - 75 Vdc
Efficiency	90.5%
Output	
Maximum power	±2.0% @ 5 V; +/-1.5% @ 3.3 V
Line regulation	0.5%
Load regulation	Single output: 0.5%
Noise/ripple	3.3 Vo: 70 mV 5.0 Vo: 50 mV
Over voltage protection Over temperature protection	Auto-restart
Switching frequency	3.3 V: 420 KHz, 5 V: 250 KHz
Temperature co-efficient	±0.02 /°C
Isolation	
I/O isolation	1500 Vdc min.

Environmental Specifications


Operating ambient temperature range	-40 °C to +85 °C
Storage temperature	-55 °C to +125 °C
Humidity	5% to 95% (non-condensing)
MTBF	2 Million hours
RoHS Compliant	

Mechanical Drawings


AVD50 BOTTOM VIEW




SIDE VIEW



TL (Surface Mount) BOTTOM VIEW



SIDE VIEW



Notes:

1. All specifications are subject to change without notice. Mechanical drawings are for reference only.
2. Label and logo appearance may vary from what is shown on mechanical drawings.

Ordering Information

Model number	Input voltage	Output voltage	Power
AVD50-48S05-6L	36 - 75 Vin	5 V @ 10 A	50 W
AVD50-48S05P-6L	36 - 75 Vin	5 V @ 10 A	50 W
AVD50-48S05SL	36 - 75 Vin	5 V @ 10 A	50 W

Notes:

Standard version is negative enable

-6 = 3.8 mm pin length

-T = Surface mount, reel tape package

-S = Surface mount, tray package

-L = RoHS 6 compliance

-P = Positive enable

Pin Assignments

Pin #	Function
1	+V in
2	Enable
3	-V in
4	-V out
5	- Sense
6	Trim
7	+Sense
8	+V out

WORLDWIDE OFFICES

Americas

2900 S.Diablo Way
Tempe, AZ 85282
USA
+1 888 412 7832

Europe (UK)

Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX
United Kingdom
+44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza
2 Wing Yip Street
Kwun Tong, Kowloon
Hong Kong
+852 2176 3333

ARTESYN
EMBEDDED TECHNOLOGIES

www.artesyn.com

Artesyn Embedded Technologies, Artesyn and the Artesyn Embedded Technologies logo are trademarks and service marks of Artesyn Embedded Technologies, Inc. All other names and logos referred to are trade names, trademarks, or registered trademarks of their respective owners. © 2016 Artesyn Embedded Technologies, Inc. All rights reserved. For full legal terms and conditions, please visit www.artesyn.com/legal.

For more information: www.artesyn.com/power
For support: productsupport.ep@artesyn.com

AVD50 Series-DS 28Aug2017