



# Cable Assemblies



172-2012-EX, 172-2024-EX, 172-2048-EX, 172-2150-EX

Cable Assemblies

172-2012-EX, 172-2024-EX, 172-2048-EX, 172-2150-EX



Dimensions

| Part No.       | A     |         | B     |         |
|----------------|-------|---------|-------|---------|
|                | (In.) | mm      | (In.) | mm      |
| 172-2012       | 8.10  | 205.74  | 12    | 304.80  |
| 172-2024       | 20.10 | 510.54  | 24    | 609.60  |
| 172-2048       | 44.10 | 1120.14 | 48    | 1219.20 |
| 172-2150       | 68.10 | 1729.24 | 72    | 1828.80 |
| RoHS Compliant |       |         |       |         |

Dimensions: mm (In.)

## RG58C/U SPECIFICATIONS

|                     |                             |
|---------------------|-----------------------------|
| Conductor:          | Tinned copper wire          |
| Insulation:         | PE                          |
| Jacket:             | PVC black                   |
| Jacket diameter:    | 5.0 mm                      |
| Capacitance:        | 98.7 pF for 1 minute @ 1KHz |
| Dielectric strength | 500V for 1 minute           |

## BNC MALE SPECIFICATIONS

|            |                      |
|------------|----------------------|
| Pin:       | Brass, silver        |
| Boot:      | PVC, black           |
| Insulator: | Delrim, white        |
| Gasket:    | Rubber, red          |
| Spring:    | S<-5, nickel         |
| Body:      | Brass, nickel plated |
| Shell:     | Brass, nickel plated |

Date Last Revised: 8-21-06

Available from Mouser Electronics  
1-800-346-6873  
www.mouser.com

KC-301043

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[172-2048-EX](#) [172-2150-EX](#) [172-2012-EX](#) [172-2024-EX](#)