

## DC-B 6-HD-M20/M20-M

Order No.: 1602067



DUPLICON, aluminum stackable housing for DUPLICON contact inserts, type B6, IP67 protection, with two locking latches, gasket and two M20 cable screw connection threads (without cable screw connection)

### Commercial data

EAN	4 046356 027762
Pack	10
Customs tariff	85369010
Country of Origin	SI
Catalog page information	Page 489 (PC-2011)

### Product notes

WEEE/RoHS-compliant since:  
05/07/2004



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### General data

Design	DC-B6
Height	37 mm
Color	pearl gray
Locking type	With locking latch

Cable exit	Lateral
Pg screw connection	None
Type of the screw connection	With 2x M20 thread
Degree of protection for housing	IP65/IP66/IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	EMC-conductive
Seal material	NBR
Material lock	Stainless steel
Material grip body interlock	PA

## Certificates



Certification

VDE-PZI


## Accessories

Item	Designation	Description
<b>General</b>		
1602326	DC-B 6-A-HD-G	DUPLICON, profile gasket for stackable housing, made of conductive EPDM
1690626	HC-K-KV-M20(8-13)	Plastic screw connection up to 5 bar, thread length: 8 mm, cable diameter: 8 - 13 mm, WAF 24, screw connection: M20
1690639	HC-K-KV-M25(11-17)	Plastic screw connection up to 5 bar, thread length: 8 mm, cable diameter: 11 - 17 mm, WAF 29, screw connection: M25
<b>Marking</b>		
0816854	EML (26,5X12)R SR	Labels for thermal transfer printers, lettering field: 26.5 mm x 12 mm, 1 roll = 2,500 labels

---

**Drawings**

Dimensioned drawing



Dimensional drawing