

Ceiling Speaker Grille Assemblies



S86T725PG8WBR



S86T725PG8WVK

Description

Bogen's Ceiling Speaker Assemblies consist of an 8" Cone Speaker (S86 or S810) pre-assembled onto a 13" steel ceiling grille painted with off-white (PG8W) or bright white (PG8U) enamel. Options for these assemblies are recessed volume control (VR), volume control with knob (VK), and rear-mounted screw terminal strip for power taps (BR).


Features

- 4-watt capacity
- 8" cone speaker for excellent audio quality
- 6 different power taps available (4, 2, 1, 1/2, 1/4, 1/8 W)
- T725 4-watt transformer
- Off-white enamel over steel grille ("W" versions)
- Bright white enamel over steel grille ("U" versions)
- Pre-assembled for faster installation
- Works with both 70V and 25V amplifier outputs
- Available with volume control – recessed or with knob (VR and VK models only)
- Screw terminals (BR models only)
- 6 oz. or 10 oz. magnet weights

Technical Specifications

Model	Power Taps (in Watts)	Frequency Response	Sensitivity (4 ft./1W)	Magnet Weight	No Volume Control	Recessed Volume Control (VR)	Volume Control w/Knob (VK)	Screw Terminals (BR)	Off-White (W)	Bright White (U)	Shipping Weight (6/Carton)	Dimensions
S86T725PG8W	4, 2, 1, 1/2, 1/4, 1/8 @ 25 & 70V	50 Hz- 12 kHz	95 dBspl	6 oz.	●				●		27 lb. / carton	13" Dia x 3-1/4" D
S86T725PG8WVR						●			●			
S86T725PG8WVK							●		●			
S86T725PG8WBR					●			●	●		28 lb. / carton	
S86T725PG8WBRVR						●		●	●			
S86T725PG8WBRVK							●	●	●			
S86T725PG8U					●					●	27 lb. / carton	
S86T725PG8UVR						●				●		
S86T725PG8UVK							●			●		
S86T725PG8UBR					●			●		●	28 lb. / carton	
S86T725PG8UBRVR						●		●		●		
S86T725PG8UBRVK							●	●		●		
S810T725PG8W	70 Hz- 15 kHz	96 dBspl	10 oz.	●				●		30 lb. / carton		
S810T725PG8WVR					●			●				
S810T725PG8WVK						●		●				
S810T725PG8U				●					●			
S810T725PG8UVR					●				●			
S810T725PG8UVK						●			●			

Ceiling Speaker Assembly Variations



Architect and Engineer Specifications

S86T725PG8W & Variations The loudspeaker assembly shall be a Bogen model **S86T725PG8W** (or **S86T725PG8WVR**, **S86T725PG8WVK**, **S86T725PG8WBR**, **S86T725PG8WBRVR**, or **S86T725PG8WBRVK**), or equivalent, 8" cone-type loudspeaker, having a frequency response of at least 50 Hz to 12 kHz. Axial sensitivity shall be 95 dB, measured at 1-watt/4 feet. The loudspeaker shall have a 6 oz. ceramic magnet and a 3/4" voice coil. A transformer, capable of matching an 8-ohm loudspeaker to a 25-volt or 70-volt line, and providing power taps of 4, 2, 1, 1/2, 1/4, and 1/8 watts shall be included. The loudspeaker shall be assembled on a 13" steel ceiling grille, finished in off-white semi-gloss enamel. Assembly depth shall be 3-1/4". (For **S86T725PG8WVR** add) A recessed volume control shall be included.

(For **S86T725PG8WVK** add) A volume control knob shall be accessible from the front of the grille.

(For **S86T725PG8WBR** add) A terminal strip shall be included for connection of the audio line.

(For **S86T725PG8WBRVR** add) A terminal strip shall be included for connection of the audio line. A recessed volume control shall be included.

(For **S86T725PG8WBRVK** add) A terminal strip shall be included for connection of the audio line. A volume control knob shall be accessible from the front of the grille.

S86T725PG8U & Variations The loudspeaker assembly shall be a Bogen model **S86T725PG8U** (or **S86T725PG8UVR**, **S86T725PG8UVK**, **S86T725PG8UBR**, **S86T725PG8UBRVR**, or **S86T725PG8UBRVK**), or equivalent, 8" cone-type loudspeaker, having a frequency response of at least 50 Hz to 12 kHz. Axial sensitivity shall be 95 dB, measured at 1-watt/4 feet. The loudspeaker shall have a 6 oz. ceramic magnet and a 3/4" voice coil. A transformer, capable of matching an 8-ohm loudspeaker to a 25-volt or 70-volt line, and providing power taps of 4, 2, 1, 1/2, 1/4, and 1/8 watts shall be included. The loudspeaker shall be assembled on a 13" steel ceiling grille, finished in bright white semi-gloss enamel. Assembly depth shall be 3-1/4".

(For **S86T725PG8UVR** add) A recessed volume control shall be included.

(For **S86T725PG8UVK** add) A volume control knob shall be accessible from the front of the grille.

(For **S86T725PG8UBR** add) A terminal strip shall be included for connection of the audio line.

(For **S86T725PG8UBRVR** add) A terminal strip shall be included for connection of the audio line. A recessed volume control shall be included.

(For **S86T725PG8UBRVK** add) A terminal strip shall be included for connection of the audio line. A volume control knob shall be accessible from the front of the grille.

S810T725PG8W & Variations The loudspeaker shall be a Bogen model **S810T725PG8W** (or **S810T725PG8WVR**, or **S810T725PG8WVK**), or equivalent, 8" cone-type loudspeaker, having a frequency response of at least 70 Hz to 15 kHz. Axial sensitivity shall be 96 dB, measured at 1-watt/4 feet. The loudspeaker shall have a 10 oz. ceramic magnet and a 1" voice coil. A transformer, capable of matching an 8-ohm loudspeaker to a 25-volt or 70-volt line, and providing power taps of 4, 2, 1, 1/2, 1/4, and 1/8 watts shall be included. The loudspeaker shall be assembled on a 13" steel ceiling grille, finished in off-white semi-gloss enamel. Assembly depth shall be 3-1/4".

(For **S810T725PG8WVR** add) A recessed volume control shall be included.

(For **S810T725PG8WVK** add) A volume control knob shall be accessible from the front of the grille.

S810T725PG8U & Variations The loudspeaker shall be a Bogen model **S810T725PG8U** (or **S810T725PG8UVR**, or **S810T725PG8UVK**), or equivalent, 8" cone-type loudspeaker, having a frequency response of at least 70 Hz to 15 kHz. Axial sensitivity shall be 96 dB, measured at 1-watt/4 feet. The loudspeaker shall have a 10 oz. ceramic magnet and a 1" voice coil. A transformer, capable of matching an 8-ohm loudspeaker to a 25-volt or 70-volt line, and providing power taps of 4, 2, 1, 1/2, 1/4, and 1/8 watts shall be included. The loudspeaker shall be assembled on a 13" steel ceiling grille, finished in bright white semi-gloss enamel. Assembly depth shall be 3-1/4".

(For **S810T725PG8UVR** add) A recessed volume control shall be included.

(For **S810T725PG8UVK** add) A volume control knob shall be accessible from the front of the grille.

BOGEN®
COMMUNICATIONS, INC.

50 Spring Street, Ramsey, NJ 07446, U.S.A.
Tel: 201-934-8500; FAX: 201-934-9832; www.bogen.com