



Date Last Revised: 10-27-05



			
.319"	.256"	.213"	.068"
8.10MM	6.50MM	5.41MM	1.72MM
FOR CRIMPING RG TYPE CABLE			
55,58,59,6,62,140,141,142,210,223,303 400,FIBER OPTIC,BELDEN 8279.			

Dimensions: mm (In.)

SPECIFICATIONS

Length: 8.7" (220±5mm)

MATERIAL

Frame:	2.8mm thickness, middle carbon steel
Die Set:	4140
Hardness:	HRC 42-48
Frame:	Black oxide finished

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

EPD-200353

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eagle Plastic Devices:](#)

[382-301C](#)