





1. HOUSING HAS AT LEAST 5 COMPLIANT KEYING LATCHING, AND POLARIZATION, TAB IS 6.30 x 0.8mm ACCORDING TO DIN 46224;
2. MATERIAL: HOUSING NYLON, UL94 V0, 750 °C GWT NO FLAME;
3. FINISH: CONTACTS, TIN PLATING OVERALL , NICKEL UNDER-PLATING;
4. PACKING: LOOSE PIECE OR TUBE. THE PART NUMBER IN THIS DRAWING ARE WITH LOOSE PIECE PACKING. PLEASE CONTACT TE SALES REPRESENTATIVES FOR TUBE PACKING REQUIREMENT.
5. PRELIMINARY, NOT FOR PRODUCTION.
6. MATERIAL: HOUSING PA66,UL94 V0  
PRODUCT COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT).
7. FINISH:CONTACT, SILVER PLATING OVERALL, NICKEL UNDER-PLATING.
8. SPECIAL VERSION: SHORT PEG DESIGN, DETAIL IN SHEET 3



|       |       |             |
|-------|-------|-------------|
| 42.30 | 40.30 | 8           |
| 37.30 | 35.30 | 7           |
| 32.30 | 30.30 | 6           |
| 27.30 | 25.30 | 5           |
| 22.30 | 20.30 | 4           |
| 17.30 | 15.30 | 3           |
| 12.30 | 10.30 | 2           |
| N     | M     | NO. OF POS. |

|                                                                                       |  |                                                                                                                                            |  |                                                                                                       |  |
|---------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>B.P<br>CHK<br>F.M<br>APR162013<br>APR162013                                                                                         |  |  TE Connectivity |  |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±.1<br>1 PLC ±0.5<br>2 PLC ±0.25<br>3 PLC ±0.013<br>4 PLC ±0.0001<br>ANGLES ±.1°<br>FINISH |  | NAME<br>RAST 5 TAB HEADER ASSY<br>DIN STYLE, TH, VERTICAL                                             |  |
|  |  | PRODUCT SPEC<br>108-106080<br>APPLICATION SPEC                                                                                             |  | SIZE<br>CAGE CODE<br>DRAWING NO<br>A200779 C=232511                                                   |  |
| MATERIAL<br>-                                                                         |  | WEIGHT<br>-                                                                                                                                |  | RESTRICTED TO<br>-                                                                                    |  |
| CUSTOMER DRAWING                                                                      |  | SCALE 1:1                                                                                                                                  |  | SHEET 1 of 3 REV 1.1                                                                                  |  |

4

3


2

1


THIS DRAWING IS UNPUBLISHED.  
 RELEASED FOR PUBLICATION  
 20

© COPYRIGHT 20 BY - ALL RIGHT REVERSED  
 ALL RIGHTS RESERVED.



| LOC | DIST | REVISIONS   |      |     |      |
|-----|------|-------------|------|-----|------|
| P   | LYR  | DESCRIPTION | DATE | DWN | APVD |
| -   | -    | SEE SHEET 1 | -    | -   | -    |
|     |      |             |      |     |      |
|     |      |             |      |     |      |




3-2232511-3  $\triangle \triangle$




2232511-5  
 1-2232511-5  $\triangle$   
 2328608-5  $\triangle \triangle$




2232511-3  
 1-2232511-3  $\triangle$   
 2328608-3  $\triangle \triangle$




2232511-4




1-2232511-4



2-2232511-5  $\triangle$



2232511-6



2232511-8

2-2232511-3  $\triangle$

3 POS.

4 POS.

4 POS.

5 POS.


VOID PIN  
 2232511-5  
 1-2232511-5

6 POS.


8 POS.

VOID PIN


PCB LAYOUT SKETCH  
 SOLDER SIDE




2232511-7  
 1-2232511-7  $\triangle$   
 2328608-7  $\triangle \triangle$



2-2232511-7  $\triangle$



3-2232511-7



PCB LAYOUT SKETCH  
 SOLDER SIDE

7 POS.

NATURE

COLOR NO. OF POS. PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±0.5

±0.13

±0.013

±0.0001

±0.0001

±0.0001

±0.0001

±0.0001

PRODUCT SPEC

108-106080

APPLICATION SPEC

-


WEIGHT

-

CUSTOMER DRAWING

SCALE

4:1



TE Connectivity

RAST 5 TAB HEADER ASSY  
 DIN STYLE, TH, VERTICAL

SIZE

CAGE CODE

DRAWING NO

A200779

C=2232511


RESTRICTED TO

-

SHEET

2 OF 3

REV A14




THE POSITION OF THE 4 PIN TAIL HOLE AND POST ARE FIXED

Ø2.50±0.05  
 HOLE FOR POLARIZING PEG


RECOMMEND PCB LAYOUT - SOLDER SIDE  
 PCB 1.5±0.2 THICK

| LOC |     | DIST        |      | REVISIONS |      |  |  |
|-----|-----|-------------|------|-----------|------|--|--|
| P   | LYR | DESCRIPTION | DATE | DWN       | APVD |  |  |
| -   | -   | SEE SHEET 1 | -    | -         | -    |  |  |
|     |     |             |      |           |      |  |  |
|     |     |             |      |           |      |  |  |
|     |     |             |      |           |      |  |  |

△ 8 SPECIAL VERSION: SHORT PEG DESIGN



SECTION C-C



OTHER DIMENSIONS SEE SHEET 1  
KEYING SEE SHEET 2

|        |             |                 |     |
|--------|-------------|-----------------|-----|
| NATURE | 7           | 2328608-7       | △ 5 |
|        | 5           | 2328608-5       | △ 5 |
|        | 3           | 2328608-3       | △ 5 |
| COLOR  | NO. OF POS. | △ 8 PART NUMBER |     |

|                                        |  |                  |           |                                                   |  |
|----------------------------------------|--|------------------|-----------|---------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>B.P.      | APRT62013 | TE Connectivity                                   |  |
| DIMENSIONS:                            |  | CHK<br>F.M.      | APRT62013 |                                                   |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD<br>-        | APRT62013 | NAME                                              |  |
| 0 PLC ±.5                              |  | PRODUCT SPEC     |           | RAST 5 TAB HEADER ASSY<br>DIN STYLE, TH, VERTICAL |  |
| 1 PLC ±0.5                             |  | 108-106080       |           |                                                   |  |
| 2 PLC ±0.25                            |  | APPLICATION SPEC |           | SIZE                                              |  |
| 3 PLC ±0.013                           |  | -                |           | CAGE CODE                                         |  |
| 4 PLC ±0.0001                          |  | WEIGHT           |           | DRAWING NO                                        |  |
| ANGLES                                 |  | -                |           | A200779                                           |  |
| FINISH                                 |  | CUSTOMER DRAWING |           | C=2232511                                         |  |
| MATERIAL                               |  | SCALE            |           | SHEET                                             |  |
| -                                      |  | 4:1              |           | 3 OF 3                                            |  |
|                                        |  |                  |           | REV                                               |  |
|                                        |  |                  |           | A14                                               |  |