


Miniature Panel Jacks

Type MPJ Glass-Filled Nylon Rated 220°C (425°F)

Glass-Filled Nylon!




FEATURES

- ✓ Compact Size
- ✓ Easy Mount
- ✓ Accessible Terminal Screws
- ✓ Color-Coded
- ✓ Accepts NEWPORT's as well as all Industry Standard Miniature Male Connectors

The MPJ Miniature Panel Jack requires less than half of the panel area required by the standard size version. A simple push-on clip is all that is required to retain the connector in a rectangular cutout, or the optional MSS snap strip can be used to mount a row. Angled terminal screws allow wiring to be done after panel assembly.

FREE! ID Number Labels and Dust Cap Supplied with Each Jack

8.1 x 16.7 mm (0.32 x 0.66") Cutout Required
 14.3 mm (0.56") Centers Horizontally
 23.8 mm (0.94") Centers Row to Row Minimum



Extra Supply of Our Patented Design Dust Caps:

Aluminum Panel Not Included
 See Panel Punches

To Order (Specify Model No.)

AlloyCode†	Type of Thermocouple Used in Connector	Compensating Alloy Used in Connector		Shell Color	Model # Female
		+	-		
K	Chromega®-Alomega®	Chromega®	Alomega®	Yellow	MPJ-K-F
T	Copper-Constantan	Copper	Constantan	Blue	MPJ-T-F
J	Iron-Constantan	Iron	Constantan	Black	MPJ-J-F
E	Chromega®-Constantan	Chromega®	Constantan	Purple	MPJ-E-F
R/S	Pt/13%Rh-Pt	Copper	Alloy #11	Green	MPJ-R/S-F
G	W-W/26%Re	Alloy #200	Alloy #226	Red	MPJ-G-F
C	W/5%Re-W/26%Re	Alloy #405	Alloy #426	Red	MPJ-C-F
D	W/3%Re-W/25%Re	Alloy #203	Alloy #225	Red	MPJ-D-F
U	Uncompensated	Copper	Copper	White	MPJ-U-F
N	OMEGALLOY®	OMEGA-P®	OMEGA-N®	Orange	MPJ-N-F

† J, K, T, E, R, S and B are ANSI designations.

OMEGALLOY®, Type N, is generically known as Nicrosil-Nisil.

Note: Type U uncompensated connectors are used with type B thermocouples (Pt/6%Rh-Pt/30%Rh)

To Order (Specify Model Number)	
Part Number	Description
MPJ-K-F	Female miniature panel jack with type K calibration
MPJ-K-F-ROHS	ROHS Female miniature panel jack with type K calibration
MPJ-T-F	Female miniature panel jack with type T calibration
MPJ-J-F	Female miniature panel jack with type J calibration
MPJ-E-F	Female miniature panel jack with type E calibration
MPJ-R/S-F	Female miniature panel jack with type R/S calibration
MPJ-G-F	Female miniature panel jack with type G calibration
MPJ-C-F	Female miniature panel jack with type C calibration
MPJ-D-F	Female miniature panel jack with type D calibration
MPJ-U-F	Female miniature panel jack with Uncompensated or type B calibration
MPJ-N-F	Female miniature panel jack with type N calibration
MPJ-CAP-12	Dust caps, pkg of 12. Other pkg sizes available
MH-MPJ-10	Extra Mounting Clips, pkg of 10. Other pkg sizes available
1-12S	Extra ID number labels for 1 thru 12. Also available for other number series.
MPJ-K-F-ROHS	Female miniature panel jack with type K calibration