



Automatic reset wrenches

- Accuracy ex works $\pm 2\%$ except - K.315DA, K.325D $\pm 4\%$.- R.304DA $\pm 6\%$.
- For use with removable accessories, such as open end and ring end, or with ratchets.
- ISO 6789

		Capacity N.m	End fitting	Graduation N.m	Dimensions wrench only		Dimensions including case		
					L (mm)	 (kg)	Case	L (mm)	 (kg)
	R.304DA	1-5	9 x 12	0,05	185	0,290	BP.D1	420	0,77
	R.306-25D	5-25	9 x 12	0,10	254	0,41	BP.D1	420	0,9
	J.306-50D	10-50	9 x 12	1,00	347	0,89	BP.D2	585	1,54
	S.306-100D	20-100	9 x 12	1,00	437	1,05	BP.D2	585	1,75
	S.306-200D	40-200	14 x 18	1,00	515	1,26	BP.D3	805	2,22
	S.306-350D	70-350	14 x 18	2,00	725	1,79	BP.D3	805	2,75
	K.315DA	120-600	14 x 18	2,00	945	4,6	BT.121A	1050	8,8
	K.325DA	200 - 1000	 30	4,00	1280	5,9	BT.K325D	1420	11,77