

YAES14K-54

Assistant Add to Favorites



YAES14K-54

16-14 NUCL. INS. RING 1/

 [Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

 [Contact our sales/technical support](mailto:info@harsco.com)

 Sample request

€ Price request

ACTIVE

Customer Drawing

RoHS
compatible

Electrical division

Download document

Literature

 > Power solutions Product Focus

 > INSULUG Brochures

 [> Renewable Energy Products Brochure](#)

 > EC&M Catalog

 > Connector Theory and Application Brochure

Application Tooling

 > Electrical Tooling

Specifications

Dimensional	Physical	Approvals / Certifications	Other Features
<u>Dimensional</u>			
Strip length (Wire)	7/32 in.		
Stud Hole (Size)	1/4 in.		
Tongue Angle	Straight		
Tongue Width (in)	0.46 in.		
Wire Shroud	No		
Insulation Diameter (Max)	0.153 in.		
<u>Physical</u>			
Conductor Size	14 AWG 16 AWG		
Conductor Type	Commercial/Military Stranded Copper		
Insulation Type	Radiation Resistant Kynar		
Color Code	Blue		
Conductor Size (Range)	16 AWG to 14 AWG		
<u>Approvals / Certifications</u>			
Military Listed	MIL-T-7928		
UL Listed	No		
CSA Certified	No		
<u>Other Features</u>			
Tongue Type	Ring		
UPC	78181081057		
Keyword	smltermHC		