




2		1				
LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			G1	REVISED PER ECO-11-004820	11MAR11	RK HMR



1 . INSULATION DIA .170 MAX

2 . FITS TAB .020 THK



—	—	—
100	LOOSE PC,BOX	8-640919-1
—	TAPE MOUNTED	640919-2
—	LOOSE PIECE	640919-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEM	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE:	—
VOLTAGE RATING:	—
CIRCULAR MIL AREA:	—

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± —
	1 PLC ± —
	2 PLC ± .015
	3 PLC ± —
	4 PLC ± —
MATERIAL BODY,BRASS .016 SLV,NYLON,COLOR,BLUE	ANGLES ± — FINISH BODY,TIN

DWN L OLMEDA 26JUN95	TE Connectivity				
CHK M ELLIS 26JUN95					
APVD B BARE 26JUN95	NAME RECEPTACLE, 187 SERIES, FASTON™, PIDG™, WIRE SIZE 16-14				
PRODUCT SPEC —	SIZE A3		CAGE CODE 00779	DRAWING NO C-640919	RESTRICTED TO —
APPLICATION SPEC —	WEIGHT —		CUSTOMER DRAWING		
SCALE NTS	SHEET 1 OF 1	REV G1			