




- 1

SIZE 22 PIN CONTACT: .030 [0.76] DIA
MAT'L: BRASS PER QQ-B-626.
- 2

RECEPTACLE HOUSING:
MAT'L: GLASS FILLED POLYETHERIMIDE RESIN.
- 3

CONDUCTOR:
24 (19/36) AWG SILVER PLATED COPPER
INSULATION: SILICONE COATED FEP; ϕ .060 ± .005 [1.52 ± 0.13]
- 4

OPERATING VOLTAGE: 12 KVDC AT 70,000 FT. ALTITUDE.
TEST VOLTAGE: 18 KVDC AT 70,000 FT. ALTITUDE.
- 5

PIGTAIL IS SOLDER DIPPED.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± .01 [0.3] 3 PLC DEC ± .005 [0.13] ANGLES ± - MATERIAL SEE CALLOUTS	DR 8-17-98 C.C.THOMAS		AMP AMP Incorporated Harrisburg, PA 17105-3608		
	CHK 8-17-98 D.EABY				
	APPD 8-17-98 D.EABY		NAME RCPT ASSY, MICRO-MINIATURE, 240 SERIES, LGH		
	APPD 8-17-98 C.C.THOMAS				
FINISH SEE CALLOUTS	PRODUCT SPEC -		SIZE	CAGE CODE	DRAWING NO
	APPLICATION SPEC -		C	00779	C-448658
	WEIGHT -		SCALE	10:1	SHEET
					1 OF 1