






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		H	REVISED PER ECR-12-001565	31JAN12	KH	TM


- 1
- WIRE RANGE: 2 WIRES OF 0.8 – 0.9 mm² [18 AWG] OR 1 WIRE OF 0.8 – 0.9 mm² [18 AWG] AND 1 WIRE OF 1.25 – 1.4 mm² [16 AWG].
- 2
- NSULATION RANGE: 2 WIRES OF 2.92 [.115] MAX DIA EACH, STACKED.
- 3
- DIMENSIONS IN BRACKETS ARE IN INCHES.



VIEW J-J
SCALE 20:1



PRE-TIN	PH.BRONZE	350557-4
PRE-TIN	BRASS	350557-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 23OCT2008		 TE Connectivity				
		CHK CASH CHRIS 23OCT2008						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MATE-N-LOK SOCKET				
		APVD CASH CHRIS 23OCT2008						
		PRODUCT SPEC —						
		APPLICATION SPEC —						
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
SEE TABLE		SEE TABLE		WEIGHT —	A2	00779	C-350557	—
CUSTOMER DRAWING				SCALE	5:1	SHEET	1 of 1	REV H