



REVISIONS				
P	DATE	DESCRIPTION	DATE	BY
K5	REVISED PER ECO-17-011152		15NOV2017	LN
RS				RS



1. FOR USE WITH, INTERCOMP RG-11/U TYPE CABLE, .068 DIA CENTER CONDUCTOR, .285 DIA DIELECTRIC, .385 O.D. JACKET, USE STRIP LENGTH A.
2. FOR USE WITH, BELDEN 8213 CABLE & THE COAX PORTION OF BELDEN 9232 CABLE, USE STRIP LENGTH B.
3. USE CRIMPING TOOL: 220015-1.
4. SEE I.S. 1914-1
5. RG-9/U, RG-9A/U, RG-9B/U, RG-214/U, RG-8/U, RG-8A/U & RG-213/U.
6. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D/RENAUD/D/SINISI



VIEW A
RECOMMENDED STRIP LENGTH
SCALE 2:1
VIEW B

OBSOLETE BY 5225886-7	RG-11/U	B	9-51713-0	225526-4	225887-2	225886-8
SUPERSEDED BY 5225886-7	TIMES FM-8	B	9-51713-0	225526-6	225887-2	225886-7
6 OBSOLETE A/A		B	9-51713-0	225596-4	225887-2	225886-6
OBSOLETE ALPHA 9847		B	51713-2	225596-4	225887-3	225886-5
SUPERSEDED BY 5225886-4		B	9-51713-4	225526-4	9-225887-0	225886-4
OBSOLETE RG-9/U,9A/U,9B/U & 214/U		B	51713-2	225596-2	9-225887-0	225886-2
SUPERSEDED BY 5225886-1		B	9-51713-4	225596-2	9-225887-0	225886-1

FOR USE WITH CABLE:	VIEW	3 FERRULE QTY=1	2 CONTACT QTY=1	1 PLUG ASSY QTY=1	PART NUMBER
---------------------	------	--------------------	--------------------	----------------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DATE: 9-18-90	BY: J. LIPPERT	CHK: 11-7-91
APPROVED BY: J. LIPPERT		
PRODUCT SPEC: 108-12020		
APPLICATION SPEC: 041 [016]		
MATERIAL: 0		
WEIGHT: 0		
CUSTOMER DRAWING: A200779		
SCALE: 4:1		
SHEET: 1 OF 1		
REV: K5		

STE TE Connectivity

PLUG, DUAL CRIMP SERIES BNC

RESTRICTED TO