



Open Racks
RR - 1367 Series



Design Features

Extra-sturdy racks made of 14 & 12 gauge steel.

Eight-inch deep welded "U" member and triangular bracket hold uprights to base (12 ga).

Panel mounting rails tapped #10-32 on E.I.A. universal spacing. (Use #7346 screws - order separately) Chassis type base, 20.87 x 26.00", drilled for RC-7758 casters. Racks may be bolted together in Add-A-Rack fashion.

Finish: Metallic Gray and Black Texture

Racks are shipped knocked down in two (2) cartons, with all necessary hardware included.

Features

Racks are shipped knocked down in two (2) cartons, with all necessary assembly hardware included.

Finishes

Finish: Black Texture (BT) and Metallic Grey

RR-1367 Series					
Catalog Number	Drawings	Panel Space	Height	Width	Weight Lbs.
RR-1367		61.25" x 19.00"	64.62"	20.87"	74
RR-1368		70.00" x 19.00"	73.37"	20.87"	77
RR-1369		77.00" x 19.00"	80.37"	20.87"	81



PART
NAME

OPEN RELAY RACK

PART
No.





RR-1367 TO RR-1369

MATERIAL:

BASE _____ 12 GA. STEEL
 SUPPORT ANGLE & RAIL ASSEMBLY _____ 14 GA. STEEL

FINISH: METALLIC GRAY OR
 BLACK TEXTURED

PANEL MOUNTING FLANGES RECESSED 3/8 IN. AND
 TAPPED #10-32 ON E.I.A. UNIVERSAL SPACING.
 MOUNTING HOLES PIERCED IN BASE FOR #RC-7758 CASTERS.
 UNIT SHIPPED UNASSEMBLED.



PART No.	A	B
RR-1367	61.375	64.703
RR-1368	70.125	73.453
RR-1369	77.125	80.453