

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190950134](#)
Status: **Active**
Description: Terminal Lugs for 14-16 AWG, Insulated Blue Sleeve, Stud Size 5 (M3), Length 21.82mm (.859")

Documents:

Drawing (PDF)	Product Specification PS-19902-013 (PDF)
Product Specification PS-19902-011 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Ring and Spade Terminals
Series	19095
Comments	Type II Insulated; Class 1 and 2
Crimp Quality Equipment	Yes
Mil-Spec	AS17143-5, MS17143-5
Product Name	Avikrimp™
Type	Ring

Physical

Barrel Type	Closed
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min - Mating	2.540µm (100µ")
Plating min - Termination	2.540µm (100µ")
Stud Size	5 (M3)
Wire Size AWG	14, 16

Material Info

Old Part Number	BB-881-2
-----------------	----------

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19095-006

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[19095Series](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the	0640050100
AT-200™ Pneumatic Hand Tool	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19095-0134