Pomona®

Model 6483 Telecom 5 Way Alligator to Right Angle Banana Plug



FEATURES:

- Multi-purpose test clips allow five ways to connect to a device under test
  - U-shaped nose for blade shaped terminals
  - Notched jaw for gripping screw heads, bare wire or terminals
  - Serrated teeth for gripping threaded or wire wrapped terminals
  - Cluster of sharp needles for piercing small gauge wires (#22-28 AWG)
  - Large piercing needle for penetrating large gauge wires

MATERIALS:

Jaws: Non-rusting Nickel Copper Alloy
Boot: Vinyl
Wire: 18 AWG , Silicone, 0.144" outside diameter
Banana Plug:
Spring: Beryllium Copper, nickel plated
Body: Brass Nickel Plated
Insulation: Polypropylene

RATINGS:

Operating Voltage: Hand-held 30 VAC/60 VDC
Hands free operation in a controlled voltage environment: 300 VRMS
Current: 8 Amperes

ORDERING INFORMATION: Model 6483-48-*
*=Color; 0-Black, 2-Red, -02 set (1 Black and 1 red lead)
Standard Length = 48" (1219,0)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (,51 mm), .xxx = ± .005" (,127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA