



Actual

Catalog Number: XC294
Product ID: 7TAA010570R0014
UPC Number: 78599190895
Status: A

Connector, Non-Insulated 90 Degree Clamp-Type, Size 1-1/4 Inch, Clamping Range 1.49 Inch - 1.85 Inch, Length 3.10 Inches, Die Cast Zinc

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Steel City
Type	Clamp Type Connectors
Special Features	Captive Two Screw
Standard	UL e1383
Size	1-1/4
Material	Zinc Die Cast

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	90°-Bend
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	Y
Material housing	Zinc die-cast
Surface protection	Untreated
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit FI	N

Packaging

Inner Quantity	3
Inner Dimensions (inches)	7.625x4.125x3.875
Outer Quantity	30
Outer Dimensions (inches)	20x9x8.5
Weight Uom	69 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com