

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35711-1100](#)
Status: **Active**
Description: 2.79mm Slip-On Receptacle Terminal, Quick Disconnect, 0.80mm Tab Thickness, Wire Range 20-22 AWG (0.52-0.33mm²), Unplated

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-35702-001 \(PDF\)](#)
[Packaging Specification PK-35711-001 \(PDF\)](#)
[Packaging Specification PK-35711-006 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR95446
UL E92853

General

Product Family Quick Disconnects
Series [35711](#)
Crimp Quality Equipment Yes
Product Name Slip-On
Type Quick Disconnect
UPC 800753937284

Physical

Barrel Type Open
Gender Female
Glow-Wire Compliant No
Insulation None
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.226/g
Orientation Straight
Packaging Type Reel
Plating min - Mating 1.016µm
Plating min - Termination 1.016µm
Polarized to Mating Part No
Tab Thickness 0.81mm
Tab Width 2.79mm
Temperature Range - Operating -40°C to +120°C
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.50-2.00mm max.
Wire Size AWG 20, 22
Wire Size mm² 0.33 - 0.52


Electrical

Voltage - Maximum Per Wire Specification

Material Info

Reference - Drawing Numbers

[Packaging Specification](#) PK-35711-001, PK-35711-006
[Product Specification](#) PS-35702-001
[Sales Drawing](#) SD-35711-11*0



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[35711Series](#)

This document was generated on 10/09/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35711-1100](#)