







REV.	DATE	DESCRIPTION
NC	10/28/99	INITIAL RELEASE
A	10/18/05	UPDATE DRAWING FORMAT AND DESCRIPTION



					UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex		
8						DRAWN	G.R.S.		10/18/05	
7	CONTACT PIN	PHOS. BRONZE	GOLD	1	UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED			PART DESCRIPTION TNC CLAMP JACK (FOR RG-8/U, 213/U, 214/U)	
6	NUT	BRASS	NICKEL	1		ISSUED				
5	WASHER	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	SHEET	1 OF 1			
4	GASKET	SILICONE	RED	1					PART NO. 122446	
3	BRAID CLAMP	BRASS	NICKEL	1						
2	INSULATOR	TEFLON	NATURAL	1						
1	BODY	BRASS	NICKEL	1						
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE C:/122/122446.DWG	DWG. NO. 122446.DWG	REV. A	SIZE A	SCALE NA

Amphenol Connex

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122446](#)