

06.63.106

Locking Support, Threaded Female

Length	10,0 mm
Material	Nylon 66
Thread Typ	M3
Dia. Hole Board	4,0 mm
Dia. Hole Chassis	3,2 mm
Typ	Support Threaded Male
UL-Flamability	UL94 HB
Board Thickness	2,10 mm
Model	Support Treaded Female
Colour	black
Design	Screw Mounting
RoHS konform / WEEE konform / 76/769/EWG konform / PAKs frei	

