

PANDUIT PART NUMBER **	PANEL THICKNESS	A ±TOL.	B ±0.015 (0.38)	C ±0.015 (0.38)	D +0.020 (0.51) -0.015 (0.38)	E REF.	F * ±TOL.	G * REF
GE_36F -C	0.026 - 0.036 (0.66 - 0.91)	0.025 ±0.010 (0.64 ±0.25)	0.045 (1.14)	0.087 (2.21)	0.030 (0.76)	0.106 (2.69)	0.060 +0.005 (0.13) -0.025 (0.64)	0.150 (3.81)
GE_62F -C	0.036 - 0.062 (0.91 - 1.57)	0.035 ±0.013 (0.89 ±0.33)	0.070 (1.78)	0.130 (3.30)	0.030 (0.76)	0.131 (3.33)	0.105 +0.005 (0.13) -0.025 (0.64)	0.150 (3.81)
GE_99F -C	0.062 - 0.099 (1.57 - 2.51)	0.054 ±0.013 (1.37 ±0.33)	0.108 (2.74)	0.155 (3.94)	0.030 (0.76)	0.169 (4.29)	0.125 +0.005 (0.13) -0.025 (0.64)	0.150 (3.81)
GE_144F -C	0.099 - 0.144 (2.51 - 3.66)	0.090 ±0.013 (2.29 ±0.33)	0.152 (3.86)	0.192 (4.88)	0.030 (0.76)	0.213 (5.41)	0.160 +0.005 (0.13) -0.035 (0.89)	0.150 (3.81)
GE_189F -C	0.144 - 0.189 (3.66 - 4.80)	0.12 ±0.030 (3.2 ±0.76)	0.206 (5.23)	0.255 (6.48)	0.046 (1.17)	0.297 (7.55)	—	—

- 3) SEE CURRENT PRICE SHEET FOR PART NO. SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 4) COLOR: a) NATURAL
b) -0 AFTER PART NO. DENOTES WEATHER RESISTANT BLACK
- 5) SLOTTED WALL STYLE IS RECOMMENDED FOR INSIDE EDGE OF PANEL CUT OUTS.
SOLID WALL STYLE IS RECOMMENDED FOR STRAIGHT, OUTSIDE EDGES.
- 6) REELS MAY CONTAIN A MAXIMUM OF THREE SPLICES.

DWG
A
SIZE

5	5/20/13	LEF	VJS	C. ADDED NOTE #6 D. TITLE BLOCK NAME CHANGE E. REPLACED TOLERANCES IN TITLE BLK	GB0239FU	5	RAMI		
4	10/18/11	SHOR	VJS	A. ADDED THICKNESS FOR GE_36F-C, B. ADDED TOLERANCES FOR A, B, C, D, & F	GB0239FU	4	RAMI		
3	2/4/03	LGG		UPDATED DIM 'A' ON GE_189F-C WAS 0.125 (3.18)	GB0239FU	3			
2	6/12/02	LGG		UPDATED DIM 'F' AS REFERENCE	GB0239FU	2			
1	4/10/02	LGG		CHG 'G' DIM TO REF	GB0239FU	1			
R	8-5-98	CPE		ADDED NOTE #5, UPDATED FILE NAME	GB0239FU	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	QC	