

Rail Mounted Terminal Blocks

0456360000

When good enough just isn't good enough

Weidmüller

ASK 1

[Email to a Friend](#)

[View Catalog Page](#)



Representative Photo

Technical Information

Clamping Type	Screw Clamp
Series	W Series
Rail Type	TS 35
Function	Disconnect
Configuration	Lever
Wire Size	#22...12 AWG
Current	15 A
Voltage	300 V
Color/Material	Beige PA

Technical Data

	UL	CSA	VDE
Rated Voltage	300 V	300 V	500 V
Rated Current	15 A	10.0 A	6.3 A
Wire Size	#22...12 AWG	#26...12 AWG	4 mm ²

Additional Data

Width/Length/Height mm (in.)	8/58/44 (.31"/2.28"/1.73")
Insulation Stripping Length mm (in.)	9 (.35")
Torque Nm (lb. in)	0.9 (8.0)
Clamping Screw	M 3
Flammability Class	UL 94 (V2)

Suggested Accessories

DIN-rail
 Ferrules
 Markers (SchT)
 Marking pens
 Marking system (WS/ZS)
 Marking tags (DEK)
 Mounting brackets
 Tools

Product Liability The above information describes our products. It does not constitute guaranteed properties and is not intended to a the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Techni data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from

Weidmüller - North America
United States 001 (800) 849-9343
Canada 001 (800) 268-4080

or

Weidmüller - Germany
Telephone operator 0049 (-5252) 960-0