



■ Specification

Model No.	Key No.	Net Weight (g)	Code No.
THA-302J-1	Without Key	584	3570
THA-302J-1K	No.2200	696	4016
	No.2000	696	3756
THA-302J-2	Without Key	559	3571
THA-302J-2K	No.2200	587	4012
	No.2000	587	3732
THA-302J-3	Without Key	388	3572
THA-302J-3K	No.2200	400	4017
	No.2000	400	3758

■ Size List

Model No.	A	B	C	D	E	F
THA-302J-1K*1	175	42	23	116.5	26.5	18
THA-302J-2K*2	142	40	23	83.5	27	18
THA-302J-3K*3	124	34	20	69	26.5	15

■ Size List for Holes

Model No.	A1	B1	C1
THA-302J-1K·1	165.5	33.5	147
THA-302J-2K·2	132.5	33.5	114
THA-302J-3K·3	114.5	28.5	99

■ Parts List

No.	Part Name	Material	Finish	Quantity
1	Body	ZDC	Cr	1
2	Handle			1
3	Shaft			1
4	Rotor Case			1
5	Packing	Elastomer	Black	1
6	Set Plate	SPCC	Zn	1
7	Square Hole Washer			1 ※
8	Flat Washer			1
9	Cross Hole Head Hexagon Bolt	S		1
10	Rotor	SUS/ZDC	—/Zn	1
11	Key	C3713	Ni	2
12	Pan Head Screw	S	Zn	1~2
13	Cam Stopper	SPCC		1

※2 pcs of washer is included for No. 7. THA-302J-3K・3.

■ Characteristic



Two segment pull out mechanism.
Protects the fingers from sudden pop out of the handle.

■ Application


Distribution boards /
Distribution panels /
Control boards /
Various types of boxes, etc.

■ Specification


It can be used for both left and right side by changing the cam 90°. The key No. is all the same. The cylinder is locked at the 180° right turn. The key can be inserted or removed from the locked and unlocked position. Waterproof by its O-ring. 60° turn handle and key No. 200 is available.



The figure shows THA-302-J-2K.
Note: The shape is slightly different
for THA-302J-1K an THA-302J-3K.



● Instruction



1. By sliding the button downward, the handle shall be popped up slightly.
2. Lift up the handle more.
3. Grip the handle tightly and turn it to open the door.