





Quartz Crystal

SMD-version

model	KX – 9A
frequency	14,31818 MHz
mode	fundamental
operating temperature	-20° ~ + 70°C
frequency tolerance at +25°C	± 30 ppm
temperature tolerance -20° ~ + 70°C	± 50 ppm
load capacitance C_L	16 pF
series resonance R_1 max.	60 Ohm
aging (first year)	± 2 ppm
shunt capacitance C_0 max.	5,0 pF
drive level in mW max.	0,05
contents of reel	1000 pcs.
RoHS	since production start
part no.	12.89008



soldering condition



(mm) reel diameter 178 mm