




SIZE	STYLE	A±.015 [0.38]	B±.005 [0.13]	C±.005 [0.13]	D±.005 [0.13]	E BSC.
E09	PIN	1.213 [30.81]	-----	.666[16.92]	.984 [24.99]	.432 [10.97]
	SOCKET		.643[16.33]	-----		
A15	PIN	1.541 [39.14]	-----	.994[25.25]	1.312 [33.32]	.756 [19.20]
	SOCKET		.971[24.66]	-----		
B25	PIN	2.088 [53.04]	-----	1.534[38.96]	1.852 [47.04]	1.304 [33.12]
	SOCKET		1.511[38.38]	-----		
C37	PIN	2.729 [69.32]	-----	2.182[55.42]	2.500 [63.50]	1.956 [49.68]
	SOCKET		2.159[54.84]	-----		

MATERIAL	DRAWN I.ESSAJEE	DATE 08/03/11	Amphenol Canada Corp.		
	DESIGNED				
	CHECKED K.LAMBIE	99/09/23			
	I. E. APPRD.				
FINISH	Q. A. APPRD.		TITLE FCC17 FILTERED D-SUB, RIGHT ANGLE .405" [10.29] F/P, PIN & SOCKET - PLASTIC MTG. BRACKET & BOARDLOCK		
	DWG. APPRD.				
	ENG. REL. NO.				
	REF. EAR C1085B				
DIMENSIONS ARE IN INCHES [mm]		CODE ID. NO. 03554	DWG. DRAWING NO. P-FCC17-XXXXB-XX0X	REV. A	
SCALE N.T.S.		WT. -----	SURF. -----	SHEET 7 OF 7	