


SPECIFICATIONS

Model Number: GL12B4
Part Number: 031074

August 11, 2005



Mechanical Drawing:



Motor:

Nominal Voltage = 12 vdc
 Operating Voltage Range = 6 - 14 vdc
 Nominal Running Current = 1.30 amps
 Locked Rotor Current = 3.00 amps
 Running Power = 16.0 watts
 Average Speed = 3200 rpm
 Bearings = Ball
 Air Flow = 150 CFM
 Acoustic = 53.6 dBA

Construction:

Venturi: Die Cast Zinc, Black
 Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 75,000 hours at 40°C.

Additional Features:

Brushless DC Motor
 Polarity Protected
 Locked Rotor Protection
 Automatic Restart Capability
 Operating Temperature -10°C to 70°C
 Storage Temperature -40 °C to 85°C

Termination:

0.110" wide Terminals Polarity Labeled

Agency Approvals:

UL, CSA, TUV