




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC., ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION	03/28/02	MCCORMICK
B	ECN 3112: UPDATE DWG FORMAT	12/14/07	D.GRIFFIN



2X BNC PLUG



NOTES:

BODY: BRASS NICKEL PLATE
CENTER PIN: BRASS GOLD PLATE
SPRING: STEEL NICKEL
WASHER: STEEL NICKEL
C TYPE WASHER: STEEL NICKEL
GASKET: PVC
INSULATOR: DERLIN
BNC SHELL: BRASS NICKEL

IMPEDANCE: 50 OHMS
FREQUENCY: 0-4 GHZ
VOLTAGE: 500 VOLTS PEAK
VSWR: 1.3 MAX

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] TOLERANCES TO BE: .X ±.1 [2.5] ANGLES ±2° .XX ±.01 [.25] .XXX ±.005 [.13] OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / - 0 > 60 [1524] +5% / - 0%	APPROVALS		DATE		01845 CONNECTIVITY PRODUCTS	A			
	DRAWN BY MCCORMICK		03/28/02				CATEGORY COAXIAL		
	CHECKED BY D.PARHAM		03/28/02				PRODUCT DESCRIPTION ADAPTOR BNC M/BNC M		
	APPROVED BY R.CARRICK		03/28/02						
PROJ 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				SIZE A	FSCM NO. 43321	DWG. NO. BA100	REV. B	
						SCALE: NONE	CAD FILE: BA100.SLDDRW	SHEET 1 OF 1	

L-com
CONNECTIVITY
PRODUCTS

45 BEECHWOOD DRIVE
NORTH ANDOVER, MA
01845

CATEGORY
COAXIAL

PRODUCT DESCRIPTION
ADAPTOR BNC M/BNC M

SIZE
A

FSCM NO.
43321

DWG. NO.
BA100

REV.
B

SCALE: NONE

CAD FILE: BA100.SLDDRW

SHEET 1 OF 1