



Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'PL1B1C0BA08M1'

Your search criteria matched only one product, shown below

PL1B1C0BA08M1



- Remote switching capability for power cycling individual outlets or a group of outlets on or off to reboot equipment or power off individual outlets to stop unauthorized use
- Per outlet monitoring provides data to determine if power allocations are accurate and the efficiency metric of any server in the data center allowing individual servers to be identified as candidates for additional capacity, redeployment, or decommissioning
- Time delay sequencing avoids circuit overload due to high in-rush current at equipment start up
- Remote access to power consumption data via a web-based GUI provides global network access to real-time power information
- Integrates with Panduit® PIM™ Software which aggregates power information through a single web based GUI
- Measure in-cabinet temperature, humidity, airflow, and dew point remotely to prevent environmental factors that can cause equipment to overheat or malfunction
- Alarm messaging capability provides user-defined alarm/messaging capabilities for specific events that exceeded thresholds

events that exceeded thresholds

- Each outlet has a green LED for indication if the outlet is on or off for easy visual identification
- Optional remote LED display available for local monitoring, part number PVQ-RD

• Part Number	PL1B1C0BA08M1
• RoHS Compliancy Status	Compliant
• Part Description	Horizontal switched power strip with per outlet power and environmental monitoring, 20 A, 208V, 8 IEC C-13 receptacles, RJ-45 Ethernet port, red LED current monitor two RJ12 remote environmental ports, and 10' power cord with NEMA 5-20P plug. UL and c-UL Listed. Dimensions: 1.7"H x 17.0"W x 8.5"D (44mm x 431mm x 220mm)
• Product Type	Horizontal Power Outlet Unit
• Color	Black
• Depth (In.)	8.5
• Depth (mm)	220
• Height (In.)	1.7
• Height (mm)	44
• Width (In.)	17.0
• Width (mm)	431
• Plug Type	NEMA 5-20P
• Pricing Description	Horizontal Switched POU with Per Outlet Power and Environmental Monitoring, 20 A, 208V, 8 IEC C-13 Rreceptacles
• Min. Order UOM	PC
• Min. Order Qty.	1
• Voltage	208
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.