






1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TUBE LOADED FOR AUTOMATIC INSERTION.
3. TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.



RECOMMENDED MOUNTING HOLE PATTERN
SCALE 4:1



SECTION A-A
SCALE 10:1

	OBSOLETE	TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640463-5
		4	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640463-4
SUPERSEDED BY 390261-2		TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640463-3
		3	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640463-2
SUPERSEDED BY 390261-2		TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640463-1

CONTACT FINISH		CONTACT MAT'L		HOUSING MATERIAL				PART NO.	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DRN 2-20-87 M.CYRUS CHG 2-20-87 R.MILLER AND 2-28-87 J.LAMBERT		AMP Tyco Electronics Corporation Harrisburg, PA 17103			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		SOCKET ASSY, DIP, 8 POS, DIPLOMATE DL -			
		0 PLC ± 1 PLC ± 2 PLC ± 4 PLC ± .005 ANGLES ±		PRODUCT SPEC 108-1066 APPLICATION SPEC 114-1049		SIZE		CASE CODE DRAWING NO A1 00779	RESTRICTED TO
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT -		C640463		OF 1	REV A
CUSTOMER DRAWING						SCALE 5:1		SHEET 1	REV A