

Company Overview

Red Rocket, Inc. is your source and solution for high density, high efficiency AC/DC power supplies. With over 30 million power supplies in service today we power the top OEM brands in a wide variety of applications from medical instruments to data-networking gear to industrial products to multimedia to security systems and more.

If thermal management, critical design space, and reduced total cost of ownership are critical to you then Red Rocket's EOS brand of open-frame and external adapters are the answer. We have a full range of standard products and also design modified standard and custom solutions for our customers. Contact us today to learn more of what Red Rocket, Inc can do to help you solve your power management needs.

Our promise to you: proven technology, quality products, first-class service, on time delivery and expert power solution advice. All our products have UL, Nemko and related safety compliance and meet RoHs standards. Call us and enjoy the Red Rocket difference.

***EOS* V-Series**


Open Frame Power Supplies 40 watts to 200 watts



Our most popular products. Award winning and performance packed.

Applications: V-Series power supplies are ideal for industrial products, data networking, telecommunications, process controls and automation products, multimedia and point of sale terminals and much more.

- Features: single and multi output products
- Power range: 40 watts to 200 watts
- Efficiency: up to 90%
- Density: up to 10 watts per cubic inch
- Sizes: 2x4x1; 3x5x1
- Universal: 90v to 240v



V-Series Open Frame AC/DC Power Supplies

High Efficiency Open Frame Power Supplies (40 to 80 W)

Part Number	Watts	Size	Voltage	Current	Efficiency
LFVLT40-1200	40	2"x4"x1"	5	8A	82%
LFVLT40-1201	40	2"x4"x1"	12	3.5A	82%
LFVLT40-1202	40	2"x4"x1"	15	2.7A	82%
LFVLT40-1203	40	2"x4"x1"	24	1.7A	82%
LFVLT40-3200	40	2"x4"x1"	5, +/-12	6A, 2A, 0.5A	82%
LFVLT40-3201	40	2"x4"x1"	5, 24, -12	6A, 1A, 0.5A	82%
LFVLT40-3202	40	2"x4"x1"	5, +/-15	6A, 1.5A, 0.5A	82%
LFVLT40-3203	40	2"x4"x1"	3v3, 5, -12	6A, 3A, 0.5A	75%
LFVLT60-1000	60	2"x4"x1"	5	10A	82%
LFVLT60-1001	60	2"x4"x1"	12	5A	87%
LFVLT60-1002	60	2"x4"x1"	15	4A	87%
LFVLT60-1003	60	2"x4"x1"	24	2.5A	87%
LFVLT60-1004	60	2"x4"x1"	48	1.25A	87%
LFVLT60-3000	60	2"x4"x1"	5, +/-12	8A, 3A, 0.5A	85%
LFVLT60-3001	60	2"x4"x1"	5, 24, -12	8A, 1.5A, 0.5A	85%
LFVLT60-3002	60	2"x4"x1"	5, +/-15	8A, 2.5A, 0.5A	85%
LFVLT60-3003	60	2"x4"x1"	3v3, 5, -12	8A, 3A, .5A	85%
LFVLT80-1000	80	3"x5"x1"	5	12A	85%
LFVLT80-1001	80	3"x5"x1"	12	6.8A	85%
LFVLT80-1002	80	3"x5"x1"	15	5.5A	85%
LFVLT80-1003	80	3"x5"x1"	24	3.4A	85%
LFVLT80-1008	80	3"x5"x1"	36	2.2A	85%
LFVLT80-1004	80	3"x5"x1"	48	1.7A	85%
LFVLT80-4000	80	3"x5"x1"	5, 12, -5, -12	10A, 2A, 0.8A, 0.8A	85%
LFVLT80-4001	80	3"x5"x1"	5, 24, +/-12	10A, 2A, 0.8A, 0.8A	85%
LFVLT80-4002	80	3"x5"x1"	5, 15, -5, -15	10A, 3A, 0.8A, 0.8A	85%
LFVLT80-4003	80	3"x5"x1"	5, 12, 24, -12	10A, 3A, 0.8A, 0.8A	85%
LFVLT80-4004	80	3"x5"x1"	3v3, 5, +/-12	10A, 3A, 0.8A, 0.8A	85%

High Efficiency Open Frame Power Supplies (100 to 200 Watts)

Part Number	Watts	Size	Voltage	Current	Efficiency
LFVLT100-1001	100	3"x5"x1"	12	7.5A	90%
LFVLT100-1002	100	3"x5"x1"	15	6.9A	89%
LFVLT100-1003	100	3"x5"x1"	24	4.2A	90%
LFVLT100-1004	100	3"x5"x1"	48	2.1A	90%
LFVLT100-4000	100	3"x5"x1"	5, 12, -5, -12	12A, 4A, 0.8A, 0.8A	86%
LFVLT100-4001	100	3"x5"x1"	5, 24, -12, 12	12A, 2A, 0.8A, 0.8A	86%
LFVLT100-4002	100	3"x5"x1"	5, 15, -15, -5	12A, 3A, 0.8A, 0.8A	86%
LFVLT100-4003	100	3"x5"x1"	5, 12, -12, 24	12A, 4A, 0.8A, .8A	86%
LFVLT110-1301	110	3"x5"x1"	12	9.2A	89%
LFVLT110-1302	110	3"x5"x1"	15	7.3A	90%
LFVLT110-1303	110	3"x5"x1"	24	4.6A	90%
LFVLT110-4300	110	3"x5"x1"	5, 12, -5, -12	15A, 4A, 1A, 1A	86%
LFVLT110-4301	110	3"x5"x1"	5, 24, -12, 12	15A, 2.75A, 1A, 1A	86%
LFVLT130-1100	130	3"x5"x1"	5	25.5A	82%
LFVLT130-1101	130	3"x5"x1"	12	10.8A	83%
LFVLT130-1102	130	3"x5"x1"	15	8.7A	83%
LFVLT130-1103	130	3"x5"x1"	24	5.4A	83%
LFVLT130-1104	130	3"x5"x1"	48	2.7A	83%
LFVLT130-4100	130	3"x5"x1"	5V, 3v3, +/-12	14A, 16A, 1.5A, 1.5A	81%
LFVLT130-4101	130	3"x5"x1"	5, 3v3, 24, -12	14A, 16A, 1.5A, 1.5A	81%
LFVLT130-4102	130	3"x5"x1"	5, 3v3, +/-15	14A, 16A, 1.5A, 1.5A	81%
LFVLT150-1100	150	3"x5"x1"	5	20/29.4A	85%
LFVLT150-1101	150	3"x5"x1"	12	8.33/12.5A	85%
LFVLT150-1103	150	3"x5"x1"	24	4.17/6.25A	85%
LFVLT150-1104	150	3"x5"x1"	48	2.08/3.17A	85%
LFVLT150-1106	150	3"x5"x1"	3v3	20/35A	85%
LFVLT150-4100	150	3"x5"x1"	5V, 3v3, +/-12	16A,19A,1.5A,1.5A	85%
LFVLT150-4101	150	3"x5"x1"	5, 3v3, 24, -12	16A,19A,.75A,1.5A	85%
LFVLT150-4102	150	3"x5"x1"	5, 3v3, +/-15	16A,19A,1.5A,1.5A	85%
LFVLT200-1001	200	3"x6.3"x1.3"	12V	16.6A	85%
LFVLT200-1002	200	3"x6.3"x1.3"	15V	13.3A	85%
LFVLT200-1003	200	3"x6.3"x1.3"	24V	8.3A	85%
LFVLT200-1004	200	3"x6.3"x1.3"	48V	4.16	85%



Eos M-Series

**Medical power supplies
Open-frame and external adapters
from 40w to 200w**

Top Supplier to leading
medical OEMs worldwide

Applications: M-Series open frame and external power supplies are ideal for medical, dental and laboratory products and systems. Endoscopes, instruments, pumps, drips, video systems, defibrillators, sleep apnea, nurse call stations and scores of other uses.

- Features: single and multi output products
- Power range: 40 watts to 200 watts
- Efficiency: up to 90%
- Density: up to 10 watts per cubic inch
- Sizes: 2x4x1; 3x5x1
- Universal: 90v to 240v input