









SECTION C
SECTION 2 : 1



TOLERANCES: $\pm 0.30\text{ mm}$ ($\pm 0.012\text{in}$)

宣义

繪圖

DRA'D BY

日期

DATE

材質

MATE.

圖名TITLE:

圖號DWG NO:

版次REVISID:

JACKY

2010/5/17

ALUMINIUM ALLOY ADC-12

HQ016

A

ITEM NO	DESCRIPTION
HQ016	NATURAL ALUMINIUM BOX<WITHOUT THE GASKET>
HQ016S	@@ IP67 RATING @@<WITH THE SILICON GASKET>
HQ016EMS	@@ IP67 RATING @@<WITH THE SILICON & SHIELDED GASKET>

MATERIAL: ALUMINUM ALLOY #ADC-12

FINISH: NATURAL (NO SUFFIX)
GRAY (SUFFIX -LG)
BLACK (SUFFIX -BK)

- 1) SIX(6) M4 x 20mm (0.787") LG. SCREWS
SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
2) ALL HOLE DIAMETERS HAVE ±0.10mm TOLERANCE
ALL OTHER DIMENSIONS HAVE ±0.30 mm TOLERANCE

宣又	繪圖	DRA'D BY	日期	DATE	材質	MATE.	圖名TITLE:	圖號DWG NO:	版次REVISID:
		JACKY		2010/5/17		ALUMINIUM ALLOY ADC-12	HQ016		A