





Modular Gang Jacks

154-6412, 154-6413, 154-6414

KOBICONN

Modular Gang Jacks

DIMENSIONS: In.



SPECIFICATIONS

Type:	6P4C, pc mount
Color:	gray
Contacts:	50 micron gold plated
Housing:	25% glass filled nylon 66
Voltage Rating:	125VAC RMS
Current Rating:	1.5A
Contact Resistance:	30mΩ max.
Insulation Resistance:	1000MΩ min. @ 500VDC
Dielectric Strength:	1000VAC RMS 60Hz for 1 minute
Operating Life:	750 cycles min.
Operation:	0°C to 70°C

Mouser Stock No.	Gang	Dimensions: In.		
		A	B	C
154-6412	2	1.11	0.96	0.433
154-6413	3	1.54	1.39	0.866
154-6414	4	1.97	1.82	1.299

Date Last Revised: 10-15-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300634

154-6412, 154-6413, 154-6414

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-6413-E](#)