








6.1	37.7	20	6		2-173268-6	4-173268-6		8-173268-6
6.1	32.7	15	5		2- ↑ -5	4- ↑ -5		8- ↑ -5
6.3	27.6	10	4		2- ↑ -4	4- ↑ -4		8- ↑ -4
6.4	22.6	5	3		2- ↓ -3	4- ↓ -3		8- ↓ -3
6.6	17.5	—	2		2-173268-2	4-173268-2		8-173268-2
"T"	"E"	"N"	極数 Pos.		黒 BLACK	青 BLUE		赤 RED
色及び型番 : COLOR & P/N								

© 19 年 日本エー・エム・ピー株式会社 © 19 BY AMP (Japan) LTD.
AMP社の諸製品は特許又は特許出願中 ALL RIGHTS RESERVED. AMP
PRODUCTS COVERED BY PATENTS
AND OR PATENTS PENDING

包含電線断面積(WIRE RANGE) mm ² (AWG)	被覆外径 (INSULATION DIA.) mm	名称 (NAME) 5/7.5 ピッチ: リセハウジング
材料 (MATERIAL) ポリプロピレンテレフタレート P.B.T. (94V-0)	仕上 (FINISH) —	一般公差 10以下 ±0.2 10を超え 30以下 ±0.25 30を超え 100以下 ±0.3 角 度 ±3°
DR. J. Inai 5/10 85	DE.	SYZE LOC 番号 (NO.) C J C-173268
CHK. J. Inai 5/10 85	APP. J. Inai 5/10 85	尺度 (SCALE) 5:1
LTR 変更 (REVISION RECORD)		REV. 0
DR. CHK. DATE		SHEET

製品仕様書 PRODUCT SPEC.	108-5171
取付適用仕様書 APPLICATION SPEC.	114-5074
取扱説明書 INSTRUCTION SHEET	IS-202J

0 RELEASED J85-8/58	DR. CHK. DATE
---------------------	---------------