

REDINGTON COUNTERS, INC.  
P.O. Box 608, 130 Addison Road, Windsor, CT 06095  
Toll Free: (860) 688-6205 • Fax: 860/688-1591  
E-Mail: [Info@RedingtonCounters.com](mailto:Info@RedingtonCounters.com) • Website: [www.RedingtonCounters.com](http://www.RedingtonCounters.com)

## Item # 711-0162, 230VAC/60Hz, 2.93 inch Dia., 3-hole round, screw termination



### 230VAC/60Hz, 2.93 inch Dia., 3-hole round, screw termination

These 7 figures, AC hour meters with running indicators, offer crisp, distinctive styling for many panel applications. Available in square and round bezel, flush mount or three-hole round panel mount. Each is light-weight, low power, and carry UL, CSA and CE approvals.

## SPECIFICATIONS

Model No.	711
Mounting	Panel (mounting hardware included)- 3-hole Round
Reset	Non-reset
Termination	1/4 inch (6.3mm) spade terminals with removable screws.
Display	7 figures, 0.14 inch high (3.6mm), 99999.99 hours
Display Height	0.14 Inch
Display Height	3.6 mm
No. of Digits	7
Records	99999.99 hours
Input Voltage	230 VAC 60 Hz &#177; 10%
Power	3 watts
Operating Temperature	-22 to +158 &#176;F
Operating Temperature	-30 to +70 &#176;C
Weight	2 oz
Weight	57 gm
Panel Cutout	1.81 Sq. Inch 1.99 Dia. Inch
Panel Cutout	46 Sq. mm 50 Dia. mm
Approvals	UL Recognized and CSA Certified. CE Approved

Stock Availability	No
Mounting Holes	Screws provided: 4-40 x 5/8 inch (16mm); Bolt hole circle: 2.44 inch (62mm)