


Item no.: 750-430/025-000
Product description: 8-CHANNEL DIGITAL INPUT MODULE DC 24 V EXT
(EXTENDED TEMPERATURE RANGE) 3,0 ms POSITIVE
SWITCHING 1-CONDUCTOR-CONNECTION



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Product group	15 (I/O System)
No. of inputs	8
CURRENT CONSUMPTION (INTERNAL)	17 mA
Signal voltage (0)	DC -3 V ... +5 V
Signal voltage (1)	DC 15 V ... 30 V
Input filter (ms)	3 ms
Current supply (typ)	2.8 mA
Isolation	500 V system / supply
Internal data width (Bit)	8 Bit
Operating temperature	-20 °C ... +60 °C
Storage temperature	-25 °C ... +85 °C
Relative air humidity	95 %
Vibration resistance	acc. IEC 60068-2-6
Shock resistance	acc. IEC 60068-2-27
Degree of protection	IP 20
Conformity marking	CE
Approvals	ATEX
Cross section [mm ²]	0.08 - 2.5 mm ²

Cross section [AWG]
Connection method
Weight
Color

28 - 14 AWG
CAGE CLAMP® CONNECTION
48.5 g
light gray



Height	64 mm
Height	2.52 in
Width	12 mm
Width	0.472 in
Depth	100 mm
Depth	3.937 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
750-430/025-000	UL	E175199 Sec.1			
750-430/025-000	UL	E198726 Sec.1			

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected