

Strain Relief

Deluxe Cord Grips

Nylon Fittings, Non-metallic Mesh, Liquidtight, for Insulated Cables and
Stainless Steel Fittings, Stainless Steel Mesh, Liquidtight, for
Insulated Cables


**Nylon Fittings Non-metallic Mesh, Liquidtight for
Insulated Cables
Straight Male Thread**

Grip Diameter Range Inches	(cm)	Thread Size N.P.T. (Inches)	Form Size	Catalog Numbers
.187"-.250"	(.47-.63)	3/8"	F1	CG304NM
.250"-.312"	(.63-.79)			CG305NM
.312"-.375"	(.79-.95)			CG306NM
.187"-.250"	(.47-.63)	1/2"	F2	CG404NM
.250"-.375"	(.63-.95)			CG406NM
.375"-.500"	(.95-1.27)			CG408NM
.375"-.500"	(.95-1.27)	3/4"	F3	CG608NM
.500"-.625"	(1.27-1.59)			CG610NM
.625"-.750"	(1.59-1.90)			CG612NM
.500"-.625"	(1.27-1.59)	1"	F4	CG810NM
.625"-.750"	(1.59-1.90)			CG812NM
.750"-.875"	(1.90-2.22)			CG814NM
.875"-.1.000"	(2.22-2.54)			CG816NM

90° Male Thread

Grip Diameter Range Inches	(cm)	Thread Size N.P.T. (Inches)	Form Size	Catalog Numbers
.250"-.375"	(.63-.95)	1/2"	F2	CG40690NM
.375"-.500"	(.95-1.27)			CG40890NM
.375"-.500"	(.95-1.27)	3/4"	F3	CG60890NM
.500"-.625"	(1.27-1.59)			CG61090NM
.625"-.750"	(1.59-1.90)			CG61290NM*
.625"-.750"	(1.59-1.90)	1"	F4	CG81290NM
.750"-.875"	(1.90-2.22)			CG81490NM

Note: Non-metallic locknuts are available upon request. Refer to page T-83.
*Cable jacket may have to be stripped to pass through connector body.

**Stainless Steel Fittings, Stainless Steel Mesh, Liquidtight, for
Insulated Cables
Straight Male Thread**

Grip Diameter Range Inches	(cm)	Thread Size N.P.T. (Inches)	Form Size	Catalog Numbers
.187"-.250"	(.47-.63)	1/2"	F2	CG404SST
.250"-.375"	(.63-.95)			CG406SST
.375"-.500"	(.95-1.27)			CG408SST
.500"-.625"	(1.27-1.59)			CG410SST
.375"-.500"	(.95-1.27)	3/4"	F3	CG608SST
.500"-.625"	(1.27-1.59)			CG610SST
.625"-.750"	(1.59-1.90)			CG612SST
.750"-.875"	(1.90-2.22)			CG614SST
.500"-.625"	(1.27-1.59)	1"	F4	CG810SST
.625"-.750"	(1.59-1.90)			CG812SST
.750"-.875"	(1.90-2.22)			CG814SST
.875"-.1.000"	(2.22-2.54)			CG816SST

Read This Data

It is important that you read all breaking strength, safety and technical data relating to this product on pages T-68 through T-74.



Straight Male



90°



Straight Male