

**HIRSCHMANN**A **BELDEN** BRAND**Product information****BAT-ANT-N-23A-V-IP65 - BAT-ANT-N-23A-V-IP65**

Industrial Ethernet:Industrial Wireless LAN:Accessories:Antenna:BAT-ANT-N-23A-V-IP65

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49859-24498-24499-64530/en/conf/uistate>

Name	BAT-ANT-N-23A-V-IP65
	Directional high gain antenna, 23 dBi for 5 GHz band.
Delivery informations	
Availability	available
Product description	
Description	Directional high gain antenna, 23 dBi for 5 GHz band.
Type	BAT-ANT-N-23A-V-IP65
Order No.	943 981-007
Cable length	1 m
Cable specification	N-plug to N-plug
Radio technology	
Range	refer to antenna distance calculator
Frequency band	5150 - 5875 MHz
Polarisation	linear, vertical
Elevation, Azimuth	3 dB beamwidth 9°
VSWR	1.5
Gain	23 dBi
Antenna connector	N female
Ambient conditions	
Operating temperature	-45 °C to +70 °C
Storage/transport temperature	-45 °C to +70 °C
Wind load	264 N at 220 km/h
Mechanical construction	
Dimensions (W x H x D)	305 x 305 x 25 mm
Mounting	wall, mast
Protection class	IP65
Material	ASA
Weight	1.5 kg
Scope of delivery and accessories	
Scope of delivery	antenna, 1 m cable, pigtail, mounting material

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.