





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. P16830	01SEP2000	-	RDR
	B	REVISED PER PCN-24-226269	10JAN2025	AJT	MB
	C	REVISED PER PCN-25-253066	25JUN2025	UBF	CB



3D VIEW



MATERIAL: CONNECTOR: PA66 GF15, GRAY
CAP: PA66 GF15, BLACK
WEDGELOCK (INCLUDED): PBT GF30 (GREEN)
BUSBAR: COPPER ALLOY, NICKEL PLATED.



THE 4 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 26 AMPS.



ORIENTATION OF "DEUTSCH" AND "-P026" TO BE OPTIONAL.



BORDER SIGNIFIES THAT PINS 1,2,7,8 AND PINS 3,4,5,6 ARE BUSSED TOGETHER WITH 4 PIN BUSBARS.

1. MATES WITH DT06-08SA-XXXX (XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR MODIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BURKE 24AUG2000	 TE Connectivity	
DIMENSIONS: INCHES[mm]		CHK L. PALLUTH 01SEP2000		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. BEARD 31AUG2000	NAME DT 8 WAY RECEPTACLE KEY ARRANGEMENT A (2) 4 PIN BUSBARS - NICKEL PLATED COLOR: GREY	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025[0,63] 4 PLC ± ANGLES ± FINISH -		PRODUCT SPEC 108-151009 APPLICATION SPEC 114-151009 WEIGHT 22 g	SIZE A2	CAGE CODE 00779
MATERIAL 5		CUSTOMER DRAWING	DRAWING NO C=DT04-08PA-P026	RESTRICTED TO -
		SCALE 3:1	SHEET 1	REV C