


T-1 Two Leaded Tri-State LED Lamps

FEATURES

- Bi-color LED lamp
- White diffused lens
- Available in ultra bright bi-color version



MAXIMUM RATINGS (Ta = 25°C)

PART NO.		FORWARD CURRENT (If) (mA)	REVERSE VOLTAGE (Vr) (V)	POWER DISSIPATION (Pd) (mW)	OPERATING TEMPERATURE (Topr) (°C)	STORAGE TEMPERATURE (Tstg) (°C)
MT2030-RG	(R)	30	5.0	85	-25~+85	-25~+100
	(G)	30	5.0	85	-25~+85	-25~+100
MT2030-HRG	(HR)	30	5.0	85	-25~+85	-25~+100
	(G)	30	5.0	85	-25~+85	-25~+100
MT2030-YG	(Y)	30	5.0	85	-25~+85	-25~+100
	(G)	30	5.0	85	-25~+85	-25~+100

OPTO-ELECTRICAL CHARACTERISTICS (Ta = 25°C)

PART NO.		MATERIAL	LENS COLOR	VIEWING ANGLE typ.	LUMIN. INT. (mcd)		FORWARD VOLTAGE (V)			REVERSE CURRENT		PEAK WAVE LENGTH
					typ.	@mA	typ.	max.	@mA	µA	Vr	nm
MT2030-RG	(R)	GaP	White Diff	118°	8.0	20	2.1	3.0	20	100	5	700
	(G)	GaP	White Diff	118°	8.3	20	2.1	3.0	20	100	5	567
MT2030-HRG	(HR)	GaAsP/GaP	White Diff	118°	9.7	20	2.1	3.0	20	100	5	635
	(G)	GaP	White Diff	118°	8.3	20	2.1	3.0	20	100	5	567
MT2030-YG	(Y)	GaAsP/GaP	White Diff	118°	7.0	20	2.1	3.0	20	100	5	585
	(G)	GaP	White Diff	118°	8.3	20	2.1	3.0	20	100	5	567



120 Broadway • Menands, New York 12204
Toll Free: (800) 98-4LED5 • Fax: (518) 432-7454