



Feed Through Terminals


DK 4QV



DK 4Q



DK 4



DK 4D



Terminal Block Selection Data

Available Options	Version	Branch	Dual Level	Dual Level	Branch with Diode
Beige Wernid					
Beige PA		0590260000* 0363660000*	0590060000* 0590160000*	0355460000 0527660000	0544660000 0396360000
Beige PA 250 Ω					
Beige PA 1000 Ω					
Blue PA		590280000* 0363680000*	0590080000* 0590180000*	0355480000 0527680000	
Beige PA Combi-foot for TS 32 and TS 35		C059026	C059006	C035546	
Blue PA Combi-foot for TS 32 and TS 35		C059028	C0390461	C035548	
10 PA terminal blocks with marking			1323860000*		

Dimensions

Width / Length / Height mm (in.)	for TS 32	6/54/60 (.24/2.13/2.36)	6/54/60 (.24/2.13/2.36)	6/50/57 (.24/1.96/2.24)	6/50/56.5 (.24/1.97/2.22)
	for TS 35	6/54/60.5 (.24/2.13/2.38)	6/54/60.5 (.24/2.13/2.38)	6/50/52.5 (.24/1.96/2.06)	6/50/56.5 (.24/1.97/2.22)
Insulation stripping length	mm (in.)	9 (.35)	9 (.35)	9 (.35)	9 (.35)

Technical Data

Rated voltage / rated current / wire size	UL	300 V / 27 A / #22...10 AWG	300 V / 27 A / #22...10 AWG	300 V / 27 A / #22...12 AWG	#22...12 AWG
	CSA	300 V / 10 A / #26...12 AWG	300 V / 5 A / #26...12 AWG		
	VDE	380 VAC / 27 A / 4 mm²	380 VAC / 27 A / 4 mm²		380 VAC
Torque	Nm (lb. in.)	.9 (8)	.9 (8)	.9 (8)	
Clamping screw	M	3	3	3	
Resistor					
Diode reverse voltage / diode current					1000 V / 1 A
Current of through busbar					10 A

Selected Accessory Data[‡]

End Plate (thickness mm)	Type	Part No.	Type	Part No.	Type	Part No.	Type	Part No.
Beige Wernid							WAP/DK 2.5	1059100000
Beige PA	AP (1.5)	1397160000	AP (1.5)	1397160000	AP (1.5)	0359260000	AP (1.5)	0359260000
Blue PA	AP (1.5)	1397180000	AP (1.5)	1397180000	AP (1.5)	0359280000		

Partition (thickness mm)

Beige Wernid	WTW (3.0)	1058800000	WTW (3.0)	1058800000	WTW (3.0)	1058800000	WTW (3.0)	1058800000
HP	TW (2.0)	0607000000	TW (2.0)	0607000000	TW (2.0)	0607000000	TW (2.0)	0607000000

Small Partition

	TSch 6	0190260000	TSch 6	0190260000	TSch 4	0363360000	TSch 4	0363360000
--	--------	------------	--------	------------	--------	------------	--------	------------

Jumpers

Q 2	0336400000	Q 2	0336400000	Q 2	0336400000	Q 2	0336400000
Q 3	0336500000	Q 3	0336500000	Q 3	0336500000	Q 3	0336500000
Q 4	0336600000	Q 4	0336600000	Q 4	0336600000	Q 4	0336600000
Q 10	0368600000	Q 10	0368600000	Q 10	0368600000	Q 10	0368600000
QB 2	0482700000	QB 2	0482700000	QB 2	0482700000	QB 2	0482700000
QB 3	0482800000	QB 3	0482800000	QB 3	0482800000	QB 3	0482800000
QB 4	0482900000	QB 4	0482900000	QB 4	0482900000	QB 4	0482900000
QB 75 bare	0526400000	QB 75 bare	0526400000	QB 75 bare	0526400000	QB 75 bare	0526400000
IP 75	0526700000	IP 75	0526700000	IP 75	0526700000	IP 75	0526700000

Switchable Jumper Links

VL 2	0446700000	VL 2	0446700000			VL 2	0446700000
BS	1056500000	VH 12.2	1056500000			VH 10	0446600000
Fixing screw	0343100000	BS	0343100000			BS M 2.5 x 14	0266800000

Test Plugs / Sockets

Test plug						PS 2.3	0180400000
Socket**						StB 8.5	0215700000

Cover

Warning label	AD 4	0303400000	AD 4	0303400000	AD 4	0303400000	AD 4	0303400000
Mounting screw	BSK M 2.5 x 18	0303300000	BSK M 2.5 x 18	0303300000	BSK M 2.5 x 18	0303300000	BSK M 2.5 x 18	0303300000
Dust cover (1 m)	ADP 2	0485300000	ADP 2	0485300000	ADP 2	0485300000	ADP 2	0485300000
Holding plate	HP 2	0485660000	HP 2	0485660000	HP 2	0485660000	HP 2	0485660000

Marking Tags

Note: Part numbers are shown for a single card of pre-printed tags numbered 1-50.	Consecutive horizontal	DEK 5/6	0468660001	DEK 5/6	0468660001	DEK 5/6	0468660001	DEK 5/6	0468660001
	Consecutive vertical	DEK 5/6	0468760001	DEK 5/6	0468760001	DEK 5/6	0468760001	DEK 5/6	0468760001

[‡]See Accessories section for additional information.
^{*}Accepts LS 2.8 shield bar (Part No. 1056400000).
^{**}Screws into tapped busbar.