


Manufacturer	MaxStream, Inc.
Part Number	A09-Y11NF
Drawing	
Specific Freq. (MHz)	895-940
Gain (dBd)	9
Maximum Power Input (Watts)	200
Product Narrative	6 element 9 dB gain yagi. 1 piece unit construction with elements welded to boom. Feed system enclosed.
Type	6-Element Yagi
General Freq. (MHz)	895-940
Bandwidth @ Rated VSWR (MHz)	45
Gain (dBi)	11.15
H. Beamwidth	65 deg.
Vert. Beamwidth	55 Deg.
Front to Back Ratio (dB)	18 dB
VSWR	1.5:1
Polarization	Vert./Horiz.
Lightning Prot.	DC Ground
Size (HxWxD")	24.75"
Weight	1.68
Rated Wind Velocity (MPH)	125
Wind Load, (sq ft)	0.26
Lateral Thrust @ RWV (lbs)	Not Specified
Bending Moment @ RWV (ft lbs)	Not Specified
Connector (direct)	None
Jumper Included	8" Pigtail w/ N Female
Connector Placement	Jumper
Mount Hdw. Incl.	U-bolt (1)
Incl. Hardware Fits	Up to 2-1/8" pipe
Warranty	1 Year
Qty/Uom	1 EACH
List (\$)	Call