



FEATURES:

- This patch cord can be used as a jumper between 0.6 (.025) sq. pins and equipment with 2.0 (.080) dia. pin jacks.

MATERIALS:

Conn: Pin Tip Plug

Material: Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Gold plated per MIL-G-45204, Type II, Class 00, over electroless nickel per MIL-C-26074, Class 1, (.0002/.0003).

Insulation: Polypropylene molded to plug body and wire.

Color: Matches color of wire.

Marking: "POMONA ELECTRONICS POMONA CALIF."

Wire: 22 AWG, stranded, 19 x 34 T.C., PVC insulated, 1.63 (.064) O.D.

Color: See Ordering Information. Marking: "POMONA 4772-XX"

Conn: .64 (.025) Square Pin Receptacle

Material: Phosphor Bronze.

Finish: Gold Plated

Housing Insulation: Polypropylene

Color: Matches color of wire.

RATINGS: Entire Assembly

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: 1000 W VDC

Current: 3 Amperes Cont.

ORDERING INFORMATION: Model 4772-XX-*

XX = Cable Lengths, Standard Lengths: 12" (305), 18" (457), 24" (610), 36" (914)

Additional lengths can be quoted upon request.

*=Color, -0 Black, -2 Red

Ordering Example: 4772-36-2 Indicates 36" in length, color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4772-24-2](#) [4772-24-0](#)