

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [73100-0071](#)
Status: **Active**
Overview: [BNC Miniature RF Connectors](#)
Description: BNC 75 Ohm, Right Angle PCB Bulkhead Jack Receptacle, Panel Isolated, White PBT Housing, Housing Height 15.90mm, Nut and Lockwasher included

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	RF/Coax Connectors
Series	73100
Comments	15.88mm Profile
Overview	BNC Miniature RF Connectors
Product Name	BNC
Style	PCB
UPC	800753686595
Wire/Cable Type	N/A


Physical	
Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	None
Net Weight	14.849/g
Orientation	Right Angle
PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
Reverse Polar	No

Electrical	
Impedance	75#

Solder Process Data	
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers	
Sales Drawing	SD-73100-0071



EU RoHS	China RoHS
RoHS Compliant RF Product	
REACH SVHC	
Not Reviewed	
Low-Halogen Status	
Low-Halogen	

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[73100Series](#)