

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [46818-0003](#)
Status: **Active**
Description: EXTreme Guardian™ Crimp Harness Housing, 3 Circuit, 11.00mm Pitch, 6 AWG

Documents:
[3D Model](#) [Product Specification PS-46819-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

TUV R72130381
UL E29179

General

Product Family Crimp Housings
Series [46818](#)
Application Wire-to-Board, Wire-to-Wire
Product Name EXTreme Guardian™
UPC 887191106335

Physical

Circuits (maximum) 3
Color - Resin Black
Flammability 94V-0
Gender Male
Glow-Wire Compliant No
Keying to Mating Part None
Material - Resin Polyester
Net Weight 15.525/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 11.00mm
Temperature Range - Operating -40°C to +105°C


Electrical

Current - Maximum per Contact 80A

Material Info

Reference - Drawing Numbers

Product Specification PS-46819-001
Sales Drawing SD-46818-001



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[46818Series](#)

Mates With
[46817](#) EXTreme Guardian™ 3 Circuit Power Plug Assembly

Use With
[46819](#) High Power Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION