




GREENLEE®
A Textron Company

MADE FOR THE TRADE!™



BIT,STEP-#2 (PKGD)

Kwik Stepper® Step Bits

Cat No: 36402

UPC No: 783310364023

Description

- Unique split-tip design penetrates through steel faster
- Resists walking or skidding, even on round surfaces
- Balanced, double-flute construction requires less pressure, does the work for you
- Designed and manufactured in USA.

Specifications

- Bit Extension : 901
- Capacity : Cut Up Through 3/8 IN (9.500 MM) Mild Steel, Copper, Brass, Aluminum, Wood, Plastic and Laminates
- Hole Size : 13/16 IN (4.800 MM), 1/4 IN (6.400 MM), 5/16 IN (7.900 MM), 3/8 IN (9.500 MM), 7/16 IN (11.100 MM), 1/2 IN (12.700 MM) (12.700 MM), 9/16 IN (14.300 MM), 5/8 IN (15.900 MM), 11/16 IN (17.500 MM), 3/4 IN (19.100MM), 13/16 IN (20.600 MM)
- Maximum Material Thickness : 3/8 IN (9.500 MM)
- Minimum Chuck Size : 3/8 IN (9.500 MM)
- Overall Length : 3-7/16 IN (87.300 MM)
- Sub Brand : Kwik Stepper
- Type : Multi Hole